

High Speed Stirrer

ZI 3007



High Speed Stirrer : ZI 3007

IS 2720 (PART IV)

SPECIFICATION:

This is for mechanical analysis and also other laboratory applications for stirring Speed approximately 4000 R.P.M. under load. A dispersion cup is supported on a rest on the stand of the stirrer and has a removable baffle. For operation on 230V A.C. supplied with dispersion cup or baffle cup.

ZEAL INTERNATIONAL

1, Netaji Subhash Marg, Darya Ganj, New Delhi-110 002 INDIA
Ph.:+91-11-23276114, 23244474, 23277528, 23278846, Fax :+91-11-23273214, 43580558
E-mail : sales@zealinternational.com ,website : zealinternational.com