info@zealinternational.com sales@zealinternational.com support@zealinternational.com quotation@zealinternational.com sit us at: www.zealinternational.com

Jaw Crusher ZI 5022

Standards:

Specification:

Features:

- Compact and rugged for laboratory and small production units
- · Designed for speed crushing
- Discharge opening adjustment range: 3 -10mm
- Manganese steel jaws adjustable up to 6 mm opening
- 250 kg materials can be crushed in approx eight hours
- Supported with strong steel frame
- Voltage: 440 V, Three Phase A.C. Supply

Laboratory Jaw Crusher Size	Feed Size	Discharge Size	Motor	Capacity
4" x 6" (100x150mm)	25 to 30mm	6mm to 20mm	3 H.P. 3 Ph.	150-200Kg/hr.
6" x 8" (150x200mm)	45 to 50mm	10mm to 22mm	5 H.P. 3 Ph.	300-400Kg/hr.
8" x 12" (200x300mm)	65 to 70mm	12mm to 25mm	7.5 H.P. 3Ph.	400-500Kg/hr.
12" x16" (300x400mm)	90 to 100mm	15mm to 30mm	10 H.P. 3 Ph.	600-750Kg/hr.
15" x24" (375x600mm)	100 to 150mm	25mm to 55mm	15 H.P. 3 Ph.	1 Ton/hr.
One Point Setting				